

# FOT-300

## OPTICAL LOSS TEST SET (OLTS)



The FOT-300 is the most optimized OLTS on the market; it offers up to three singlemode or two multimode wavelengths on a single port.

### KEY FEATURES

Highly optimized OLTS integrating a power meter port and up to three singlemode sources or two multimode sources on a single port

Power autonomy of 260 hours

Three-year warranty and recommended calibration interval, for dramatically reduced cost of ownership

Ergonomic, eye-catching handheld package

## AUTO-WAVELENGTH RECOGNITION

The FOT-300's built-in source can transmit with a wavelength-identification digital encrypted protocol, so that any compatible unit—the FPM-300 power meter and the FOT-300's receiver—can automatically use the proper calibration parameters. This feature reduces the need for communication between the two technicians and decreases the potential for error.

## DISTANT REFERENCING

Signal encrypting can also give the receiving end information on the power to be used as reference, helping ensure efficient referencing, even when the two units are far apart.

## NO OFFSET NULLING

Thanks to its unique design, the FOT-300 OLTS reduces measurement time in typical measurement situations, as the need for an offset nulling is eliminated.

## FTTx-READY

EXFO's FOT-300 allows for the testing of passive optical networks (PONs) at 1310 nm, 1490 nm and 1550 nm, the three wavelengths recommended by the ITU-T (G.983.3) for PONs.

SPECIFICATIONS <sup>a</sup>			
Model	FOT-302	FOT-302X	
Power meter port <sup>b</sup>	Ge	GeX	
Power range (dBm) <sup>c</sup>	10 to -60	26 to -50	
Range displayed (dBm)	Down to -65	Down to -50	
Number of calibrated wavelengths <sup>d</sup>	10	10	
Power uncertainty <sup>e</sup>	±5 % ± 1 nW	±5 % ± 1 nW	
Resolution (dB)	0.01 <sup>f</sup>	0.01 <sup>g</sup>	
Automatic offset nulling <sup>h</sup>	Yes	Yes	
Warmup time (s) <sup>h,i</sup>	0	0	
Display units	dB/dBm/W	dB/dBm/W	
Automatic wavelength recognition <sup>i</sup>	Yes	Yes	
Screen refresh rate (Hz)	3	3	
Tone detection (Hz)	270, 1 k, 2 k	270, 1 k, 2 k	
Battery life (hours) (typical)	260	260	
Warranty and recommended calibration interval (years)	3	3	
Model <sup>k</sup>	23BL	12D	235BL
Central wavelength (nm)	1310 ± 20 1550 ± 20	850 ± 25 1300 + 50/-20	1310 ± 20 1490 ± 10 1550 ± 20
Spectral width (nm) <sup>l</sup>	≤5	50/135	≤5
Output power (dBm)	≥1/≥1	≥-20/≥-20 (62.5/125 μm)	≥1/≥-4.5/≥-3
Power stability (dB) <sup>m</sup> 8 h	±0.1	±0.1	±0.1
Battery life (hours) <sup>n</sup>	120	120	120
Automatic wavelength recognition	Yes	Yes	Yes
Tone generation (Hz)	270, 1 k, 2 k	270, 1 k, 2 k	270, 1 k, 2 k
Warranty and recommended calibration interval (years)	3	3	3

a. Guaranteed unless otherwise specified.

b. All specifications valid at 1550 nm and 23 °C ± 1 °C, with an FC connector.

c. In CW mode; sensitivity defined as 6 x rms noise level.

d. Wavelengths: 830 nm, 850 nm, 980 nm, 1300 nm, 1310 nm, 1450 nm, 1490 nm, 1550 nm, 1590 nm and 1625 nm.

e. Traceable to national standards; FOT-302X: up to 20 dBm.

f. From 10 dBm to -50 dBm.

g. From 26 dBm to -35 dBm.

h. Power of > -40 dBm for FOT-302, and of > -25 dBm for FOT-302X.

i. For ±0.05 dB, from 18 °C to 28 °C.

j. At 850 nm, 1300 nm, 1310 nm, 1490 nm, 1550 nm and 1625 nm; power > -50 dBm for FOT-302, and > -40 dBm (typical) for FOT-302X.

k. All specifications valid at 23 °C ± 1 °C, with an FC connector.

l. rms for lasers and -3 dB width for LEDs; typical values for LEDs.

m. After a 15-minute warmup; expressed as ± half the difference between the maximum and minimum values measured during the period, with an APC connector on the power meter.

n. Typical autonomy in Auto mode.

## GENERAL SPECIFICATIONS

Size (H x W x D)	185 mm x 100 mm x 55 mm (7 1/4 in x 4 in x 2 1/8 in)
Weight	0.4 kg (0.9 lb)
Temperature	Operating: -10 °C to 50 °C (14 °F to 122 °F) Storage: -40 °C to 70 °C (-40 °F to 158 °F)
Relative humidity	0 % to 95 % non-condensing

## LASER SAFETY



## STANDARD ACCESSORIES

User guide, certificate of calibration, instrument stickers in six languages, AC adapter, EUI-XX, connector adapter (FOA-XX), AA batteries (3), wrist strap, alcohol cleaning pads

## ORDERING INFORMATION

### FOT-30X-XX-XX

#### Model

FOT-302-12D = Ge detector, 850/1300 nm LED source 62.5/125 μm  
 FOT-302X-23BL = High-power Ge detector,  
 1310/1550 nm laser source 9/125 μm  
 FOT-302X-235BL = High-power Ge detector,  
 1310/1490/1550 nm laser source 9/125 μm

#### Connector

EI-EUI-28 = UPC/DIN 47256  
 EI-EUI-76 = UPC/HMS-10/AG  
 EI-EUI-89 = UPC/FC narrow key  
 EI-EUI-90 = UPC/ST  
 EI-EUI-91 = UPC/SC  
 EI-EUI-95 = UPC/E-2000

#### Connector adapter

FOA-12 = Biconic  
 FOA-14 = D4, D4/PC  
 FOA-16 = SMA/905, SMA/906  
 FOA-22 = FC (PC/SPC/UPC/APC), NEC-D3  
 FOA-28 = DIN 47256 (LSA): DIN 47256 (PC/APC)  
 FOA-32 = ST (PC/SPC/UPC)  
 FOA-54 = SC (PC/SPC/UPC/APC)  
 FOA-78 = Radiall EC  
 FOA-96B = E-2000  
 FOA-98 = LC  
 FOA-99 = MU

Example: FOT-302X-235BL-FOA-22-EI-EUI-89

**EXFO headquarters** T +1 418 683-0211 **Toll-free** +1 800 663-3936 (USA and Canada)

EXFO serves over 2000 customers in more than 100 countries. To find your local office contact details, please go to [www.EXFO.com/contact](http://www.EXFO.com/contact).

EXFO is certified ISO 9001 and attests to the quality of these products. EXFO has made every effort to ensure that the information contained in this specification sheet is accurate. However, we accept no responsibility for any errors or omissions, and we reserve the right to modify design, characteristics and products at any time without obligation. Units of measurement in this document conform to SI standards and practices. In addition, all of EXFO's manufactured products are compliant with the European Union's WEEE directive. For more information, please visit [www.EXFO.com/recycle](http://www.EXFO.com/recycle). **Contact EXFO for prices and availability or to obtain the phone number of your local EXFO distributor.**

For the most recent version of this spec sheet, please go to [www.EXFO.com/specs](http://www.EXFO.com/specs).

In case of discrepancy, the web version takes precedence over any printed literature.